

Objective list

| Objective | Working distance | Location | Cat code | Dic Slider |
|--|----------------------------|----------|-----------------|--|
| 5x/0.16 Ph1 EC Plan-Neofluar | WD=18.5mm | All | 420331-9911 | Phase 1 |
| 10x/0.3 Ph1 EC Plan-Neofluar | WD=5.2mm | All | 420341-9911 | Phase 1 |
| 10x/0.3 EC Plan-Neofluar | WD=5.2mm | HH | 420340-9901 | |
| 10x/0.5 Fluar | WD=1.6mm | All | 420140-9901 | |
| 10x/0.45 DIC Plan-Apochromat | WD=2mm | HH | 420640-9900 | 1045-073 DIC Slider Plan-Apo 10x/0.45 II |
| LD Plan- Neofluar 20x 0.40 KORR | 7.9 at cover glass 0.75 | SAF | 441340-9970 | |
| 20x/0.8 DIC Plan Apochromat | WD=0.55mm | All | 420650-9901 | 426940 DIC Slider EC PN 10x 20x/PA 20x |
| 40x/0.55 Ph2 LD A-Plan | WD=2.0mm | All | 421261-9915 | Phase 2 |
| LD Achroplan 40x 0.60 KORR Ph2 | 1.8 at coverglass 1.0 | SAF | 440865-0000 | Phase 2 |
| 40x/0.75 Ph2 EC Plan-Neofluar | WD=0.71mm | All | 420361-9910 | Phase 2 |
| 40x/1.30 Oil DIC EC Plan-Neofluar | WD=0.21mm | All | 420462-9900 | 426944 DIC Slider PN 40x, F 40x, PA 40x |
| 63x/1.20 W corr UV-VIS-IR C-Apochromat | WD=0.28mm | All | 421787-9970 | 426946 DIC Slider PN63x CApo63x |
| 63x/1.40 Oil DIC Plan-Apochromat | WD=0.19mm | All | 420782-9900-720 | 426957 DIC slider Planapo 63x/1.40 III |
| Plan- Apochromat 63x 1.40 Oil Ph3 | WD= 0.19mm | SAF | 420781-9910 | Phase 3 |
| 100x/1.4 Oil Ph3 Plan Apochromat | WD= 0.17mm | HH | 420791-9910 | Phase 3 |

| | | | | |
|---------------------------------------|------------|-----|-----------------|-------------------------------------|
| 100x/1.4 Oil Ph3 Plan Achromat | WD= 0.17mm | SAF | 440781-9904 | Phase 3 |
| α -Plan-Fluar 100x 1.45 Oil | WD= 0.11mm | SAF | 1084-514 | |
| APO Calibration (5x) | N/A | HH | 420639-9000-700 | Calibration & Pin-hole alignment |